Product data sheet

Specification





communication module Profibus DP V1, Altivar, 12Mbps, 1 female SUB D9 connector

VW3A3607

Product availability: Stock - Normally stocked in distribution facility

Price*: 281.36 USD

Main

Range Of Product	Altivar
Product Or Component Type	Communication module
Accessory / Separate Part Category	Communication accessories

Complementary

Product Compatibility	Lexium 32M
Range Compatibility	Altivar 32
	Altivar Machine ATV340 except Sercos drives
	Altivar Easy 610
	Lexium 32
	Altivar Process ATV900
	Altivar Process ATV600
	Altivar Machine ATV320
	Altivar Process Modular
Communication Port Protocol	Profibus DP V1
Electrical Connection 1 female connector SUB-D 9	
Transmission Rate	9.6 kbps12 Mbps
Addressing	1126 configurable by graphic terminal/SoMove software
	Configuration settings
Communication Service	4 configurable telegrams
	Mapping of the process data from the master
	Parameters management compliant with PROFIdrive V4.1
	Several DP V1 messaging modes
	Drive profile native ATV32 IEC 61800-7-201 (CiA 402)
Display Type	1 LED RUN
	1 LED bus fault (BF)
Diagnostic Function	Diagnostic data with VSD status
	Host drive handled from two masters (MS0 and MS1)
	Standard identification and maintenance requests
Bus Profile	PROFIdrive
	CiA 402

Environment

Standards IEC 61800-7-201 (CiA 402)

Ordering and shipping details

Category	US1PC5118263	
Discount Schedule	PC51	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Gtin	3606480177583	
Returnability	Yes	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.85 in (4.700 cm)	
Package 1 Width	2.40 in (6.100 cm)	
Package 1 Length	3.54 in (9.000 cm)	
Package 1 Weight	2.15 oz (61.000 g)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	100	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	ckage 2 Weight 14.65 lb(US) (6.643 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes
②	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov