Product data sheet





communication module DeviceNet, Altivar, 500kbps, 1 removable 5 way screw connector

VW3A3609

Product availability: Stock - Normally stocked in distribution

Price*: 552.60 USD

Main

Range Of Product	Altivar
Product Or Component Type	Communication module

Complementary

Complementary		
Range Compatibility	Altivar Process Modular Altivar 32 Altivar Process ATV600 Altivar Machine ATV340 except Sercos drives Altivar Process ATV900 Altivar Machine ATV320	
Communication Port Protocol	DeviceNet	
Electrical Connection	1 connector 1 removable 5-way screw connector	
Transmission Rate	125 kbps, 250 kbps and 500 kbps configurable	
Maximum Cable Distance Between Devices	328.08 ft (100 m) 500 kbps 1640.42 ft (500 m) 125 kbps	
Addressing	sing 163 configurable by graphic terminal/SoMove software	
Communication Service	Inputs : polled, change of state, cyclic Outputs : polled ODVA AC drive and CiA 402 profile Auto device replacement Communication monitoring time out adjustable by DeviceNet configurator	
Display Type	1 LED MS (Module Status) 1 LED NS (Network Status)	
Diagnostic Function	Control mode received by graphic terminal Received instruction by graphic terminal	
Bus Profile	CIP AC Drive CiA 402	
Net Weight	0.66 lb(US) (0.3 kg)	

Ordering and shipping details

Category	US1CP4B22152	
Discount Schedule	CP4B	
Gtin	3606480198991	
Returnability	Yes	
Country Of Origin	SE	

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	1.85 in (4.700 cm)	
Package 1 Width	2.44 in (6.200 cm)	
Package 1 Length	age 1 Length 3.50 in (8.900 cm)	
Package 1 Weight	age 1 Weight 2.36 oz (67.000 g)	
Unit Type Of Package 2	S03	
Number Of Units In Package 2	100	
Package 2 Height	11.81 in (30.000 cm)	
Package 2 Width	11.81 in (30.000 cm)	
Package 2 Length	15.75 in (40.000 cm)	
Package 2 Weight	15.65 lb(US) (7.098 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Toxic Heavy Metal Free	
⊘	Mercury Free	
②	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov