Product data sheet

Specifications





Altivar

Communication module

communication module Modbus TCP and Ethernet IP, Altivar, 10 or 100Mbps, 2 x RJ45 connectors

VW3A3616

Product availability: Stock - Normally stocked in distribution facility

Price*: 250.00 USD

Main

Range Of Product

Product Or Component Type

Accessory / Separate Part Category	Communication accessories	
Complementary		
Product Compatibility	Lexium 32M	
Range Compatibility	Altivar Machine ATV320 Altivar 32 Lexium 32	
Communication Port Protocol	Modbus TCP EtherNet/IP	
Electrical Connection	1 connector RJ45, EtherNet/IP 1 connector RJ45, Modbus TCP	
Transmission Rate	10/100 Mbps	
Addressing	IP addressing manual, BOOTP or DHCP	
Exchange Mode	Half duplex and full duplex	
Communication Service	Up to 8 connections (includes connections of Modbus TCP/Ethernet IP/ Modbus TCP FDR Agent Ethernet IP/Modbus TCP Read holding registers (03), 63 words max Modbus TCP Read input registers (04), 63 words max Modbus TCP Write single register (06) Modbus TCP Write multiple registers (16), 63 words max Modbus TCP Read/write multiple registers (23) Modbus TCP Read device identification (43) Modbus TCP Diagnostics (08) Modbus TCP Diagnostics (08) Modbus TCP I/O scanner : read/write, 6 words maximum Modbus TCP Communication monitoring Modbus TCP SNMP agent Ethernet IP Master/Slave hierarchy ODVA AC drive profile and CiA 402 profile Ethernet IP Fixed communication monitoring adjusted by Ethernet IP scanner adaptor (Master) Ethernet IP	
Display Type	1 LED MS (Module Status) 1 LED NS (Network Status)	

Ordering and shipping details

Net Weight

Category	US1PC5118263
Discount Schedule	PC51

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

1 LED Ethernet port activity 1 LED Modbus TCP port activity

0.66 lb(US) (0.3 kg)

Gtin	3606480177590
Returnability	Yes
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.65 in (4.200 cm)
Package 1 Width	2.40 in (6.100 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	2.12 oz (60.000 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	100
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	14.53 lb(US) (6.590 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
Ø	Rohs Exemption Information Yes	
Ø	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov