

Product data sheet

Specifications



Auxiliary contact block, TeSys Control, 1 NC early break+1 NO late make, for V02-V6

VZ7

Product availability: Stock - Normally stocked in distribution facility

Price*: 42.80 USD

Main

Range	TeSys
Device Short Name	VZ
Product Or Component Type	Auxiliary contact block
Performance Level	High performance
Contacts Type And Composition	1 NO + 1 NC
Contact Operation	Late-make 1 NO Early-break 1 NC
Product Compatibility	V2 V5 V02 V6 V1 V4 V01 V0 V3
Network Type	AC DC
Network Frequency	50/60 Hz

Complementary

Mounting Location	Left Right
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ith] Conventional Free Air Thermal Current	12 A
[Ithe] Conventional Enclosed Thermal Current	10 A
Mechanical Durability	100000 cycles
Electrical Durability	30000 cycles DC-11 100000 cycles AC-15
Connections - Terminals	screw clamp terminals 2 0.00...0.00 in² (0.75...1.5 mm²) flexible - with cable end screw clamp terminals 2 0.00...0.00 in² (1...2.5 mm²) solid
Tightening Torque	6.20 lbf.in (0.7 N.m) screw clamp terminals
Height	2.56 in (65 mm)
Width	0.79 in (20 mm)
Depth	1.91 in (48.5 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.11 lb(US) (0.05 kg)
------------	-----------------------

Environment

Standards	IEC 60947-5
Product Certifications	GL CSA UL UKCA
Protective Treatment	TC
Ip Degree Of Protection	IP20 conforming to IEC 60529
Ambient Air Temperature For Operation	-4...122 °F (-20...50 °C)
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1

Ordering and shipping details

Category	US10CP121730
Discount Schedule	0CP1
Gtin	3389110551969
Returnability	Yes
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	1.46 in (3.7 cm)
Package 1 Length	3.54 in (9.0 cm)
Package 1 Weight	1.83 oz (52.0 g)
Unit Type Of Package 2	S02
Number Of Units In Package 2	69
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	8.67 lb(US) (3.931 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

 Pvc Free

 Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations