

# Product data sheet

Specifications



booted head for pushbutton XAC-B - yellow - 16 mm, -25..+70 °C

XACB9215

Product availability: Non-Stock - Not normally stocked in distribution facility

! Discontinued

## Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACB
Marking	Unmarked
Operator Additional Information	Booted
Operating Travel	0.63 in (16 mm)
Cap/Operator Or Lens Colour	Yellow
Product Compatibility	XESD1191 XESD1181 XESD1281 XESD1291
Sale Per Indivisible Quantity	10

## Complementary

Net Weight	0.01 lb(US) (0.005 kg)
------------	------------------------

## Environment

Standards	IEC 60947-5-1 CSA C22.2 No 14 IEC 60947-5-1
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)(IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to IEC 62262

## Ordering and shipping details

Category	US10CS222473
Discount Schedule	0CS2
Gtin	3389110641004
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	FR
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.92 in (12.5 cm)
Package 1 Width	0.79 in (2.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.25 oz (7.0 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	4.92 in (12.5 cm)
Package 2 Width	0.79 in (2.0 cm)
Package 2 Length	3.94 in (10.0 cm)
Package 2 Weight	2.57 oz (73.0 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a>
California Proposition 65		WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>