

Product data sheet

Specifications



booted head for pushbutton XAC-B -
green - 16 mm, -40..+70 °C

XACB9223

⚠ Discontinued on: Jul 5, 2023

Product availability: Non-Stock - Not normally stocked in
distribution facility

⚠ Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACB
Marking	Unmarked
Operator Additional Information	Booted
Operating Travel	0.63 in (16 mm)
Cap/Operator Or Lens Colour	Green
Product Compatibility	XESD1291 XESD1281 XESD1191 XESD1181
Sale Per Indivisible Quantity	10

Complementary

Net Weight	0.01 lb(US) (0.005 kg)
------------	------------------------

Environment

Standards	IEC 60947-5-1 EN 60947-5-1 CSA C22.2 No 14
Ambient Air Temperature For Operation	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)(IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102

Ordering and shipping details

Category	US1000T18407
Discount Schedule	000T
Gtin	3389110644746
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	FR
-------------------	----

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.94 in (10.0 cm)
Package 1 Width	1.57 in (4.0 cm)
Package 1 Length	3.94 in (10.0 cm)
Package 1 Weight	0.21 oz (6.0 g)
Unit Type Of Package 2	BAG
Number Of Units In Package 2	10
Package 2 Height	3.94 in (10.0 cm)
Package 2 Width	1.57 in (4.0 cm)
Package 2 Length	3.94 in (10.0 cm)
Package 2 Weight	2.19 oz (62.0 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration
California Proposition 65		WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov