Product data sheet





Empty control station without hinges, Harmony XAP, XB2 SL, plastic, grey, 2 cut outs, 22mm

XAPA1120

Product availability: Stock - Normally stocked in distribution

Price*: 114.00 USD

Main

Range Of Product	Harmony XAP			
Product Or Component Type	Empty control station without hinges			
Device Short Name	XAPA			
Product Destination	For Ø 22 mm control and signalling units			
Product Front Plate Size	85 x 146 mm			
Usable Depth	3.27 in (83 mm)			
Number Of Cut-Out	4 cut-outs			
Colour Of Base Of Enclosure	Grey			
Colour Of Cover	Grey			
Material	Glass reinforced polyester			
Cable Entry	Undrilled			
Device Mounting	Flush			
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K			
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to petrol High resistant to sea water			

Complementary

Number Of Vertical Rows	1		
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94		
Net Weight	1.01.lb(US) (0.46 kg)		

Environment

Protective Treatment	TC TH	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Overvoltage Category	Class II IEC 60536 Class II NF C 20-030
Fire Resistance	1562 °F (850 °C) NF C 20-455 1760 °F (960 °C) IEC 92

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389110313147
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	5.31 in (13.500 cm)			
Package 1 Width	3.54 in (9.000 cm)			
Package 1 Length	6.10 in (15.500 cm)			
Package 1 Weight	17.85 oz (506.000 g)			
Unit Type Of Package 2	S03			
Number Of Units In Package 2	12			
Package 2 Height	11.81 in (30.000 cm)			
Package 2 Width	11.81 in (30.000 cm)			
Package 2 Length	15.75 in (40.000 cm)			
Package 2 Weight	14.37 lb(US) (6.520 kg)			
Unit Type Of Package 3	P06			
Number Of Units In Package 3	96			
Package 3 Height	29.53 in (75.000 cm)			
Package 3 Width	23.62 in (60.000 cm)			
Package 3 Length	31.50 in (80.000 cm)			
Package 3 Weight	138.41 lb(US) (62.780 kg)			

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
Ø	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

Dimensions Drawings

Dimensions and Fixing



- (2) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 12 mm/0.47 in.
- P Usable depth

а		b		G		Н	
mm	in.	mm	in.	mm	in.	mm	in.
85	3.35	146	5.75	70	2.76	105	4.13

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions



b1 Vertical interaxis: 40 mm/1.57 in.