
# Product data sheet

Specification





Empty control station without hinges, Harmony XAP, plastic, grey, 16 cut outs, 22mm, 151 x 241 x 83mm

XAPA3116

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 390.00 USD

### Main

Range Of Product	Harmony XAP				
Product Or Component Type	Empty control station without hinges				
Device Short Name	XAPA				
Product Destination	For Ø 22 mm control and signalling units				
Product Front Plate Size	151 x 241 mm				
Usable Depth	3.27 in (83 mm)				
Number Of Cut-Out	16 cut-outs				
Colour Of Base Of Enclosure	Grey				
Colour Of Cover	Grey				
Material	Glass reinforced polyester				
Cable Entry	Undrilled				
Device Mounting	Flush				
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K				
Resistance To Chemical Agents	High resistant to acids High resistant to all solvents High resistant to bases High resistant to diesel High resistant to mineral salts High resistant to oils and greases High resistant to sea water				

## Complementary

Number Of Vertical Rows	4		
Flame Retardance	M3 conforming to CSTB VO conforming to UL 94		
Net Weight	1.81 lb(US) (0.82 kg)		

#### **Environment**

Protective Treatment	TH TC		
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)		

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Operation	-40158 °F (-4070 °C)		
Overvoltage Category	Class II IEC 60536 Class II NF C 20-030		
Fire Resistance	1562 °F (850 °C) NF C 20-455		

# Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389110313215
Returnability	No
Country Of Origin	FR

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.12 in (13 cm)
Package 1 Width	6.54 in (16.6 cm)
Package 1 Length	9.61 in (24.4 cm)
Package 1 Weight	34.78 oz (986 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	9.80 lb(US) (4.445 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>9</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
Eu Rohs Directive					
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

### **Dimensions Drawings**

### **Dimensions and Fixing**




- (2)  $2 \times \emptyset$  5.6 mm/0.22 in. holes, depth 12 mm/0.47 in.
- P Usable depth

а		b		G		H .	
mm	in.	mm	in.	mm	in.	mm	in.
151	5.94	241	9.49	135	5.31	200	7.87

Refer to the product characteristics to get the number of cut-outs.

Cut-out interaxis dimensions (vertical mounting)



- b1 Vertical interaxis: 40 mm/1.57 in.
- b2 Horizontal interaxis: 30 mm/1.18 in.