


Product data sheet

Specifications



drilled front plate - XAP-E - metal - 4 opening

XAPE104

⚠ Discontinued on: Mar 31, 2020

⚠ Discontinued

Main

Range Of Product	Harmony XAP
Product Or Component Type	Front plate with fixing screws
Device Short Name	XAPE
Product Destination	For Ø 22 mm control and signalling units
Product Front Plate Size	72 x 171 mm
Number Of Cut-Out	4 cut-outs
Material	Anodised aluminium
Device Mounting	Flush
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts

Complementary

Net Weight	0.21 lb(US) (0.095 kg)
------------	------------------------

Environment

Protective Treatment	TH TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030

Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389118115880
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.91 in (15 cm)
Package 1 Width	11.81 in (30 cm)
Package 1 Length	15.75 in (40 cm)
Package 1 Weight	3.35 oz (95 g)

Contractual warranty

Warranty	18 months
----------	-----------