Product data sheet

Specifications





Protective rear cover, Harmony XAP, for plastron XAPE305, insulated material, without opening, IP 65

XAPE905

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 60.00 USD

Main

Range Of Product	Harmony XAP		
Product Or Component Type	Protective rear cover		
Device Short Name	ХАРЕ		
Product Destination	For front plate XAPE305		
Material	Insulated material		
Cable Entry	Knock-out cable entries		
Product Mounting	Flush mounting		
Ip Degree Of Protection	IP65 IEC 60529 IP657 NF C 20-010		
Resistance To Chemical Agents	Good resistant to acetone Good resistant to alcohols Good resistant to chloride and fluoride solvents Good resistant to diluted mineral acids Good resistant to oils and petrol Good resistant to organic acids Good resistant to salts		

Complementary

Net Weight	0.18 lb(US) (0.08 kg)	
Environment		
Protective Treatment	TC TH	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030	

Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389110628180
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Packing Units

PCE
1
2.68 in (6.800 cm)
3.82 in (9.700 cm)
7.60 in (19.300 cm)
4.09 oz (116.000 g)
\$02
12
5.91 in (15.000 cm)
11.81 in (30.000 cm)
15.75 in (40.000 cm)
3.73 lb(US) (1.690 kg)
P06
96
17.72 in (45.000 cm)
31.50 in (80.000 cm)
23.62 in (60.000 cm)
50.68 lb(US) (22.988 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


Certifications & Standards

Reach Regulation	REACh Declaration		
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration		
China Rohs Regulation	China RoHS declaration		
Environmental Disclosure	Product Environmental Profile		
Circularity Profile	No need of specific recycling operations		
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov		

Product data sheet

Dimensions Drawings

Dimensions and Mounting



P Usable depth

b		Р	
mm	in.	mm	in.
184	7.24	82.5	3.25