Product data sheet

Specification





① Discontinued

Harmony XAP, Empty control station, zinc alloy, grey, 2 cut-outs, Ø22, 80 x 80 x 77 mm

XAPG19802

- ! Discontinued on: Dec 2, 2020
- ! End-of-service on: Dec 31, 2020

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Range Of Product | Harmony XAP | |
|-------------------------------|--|--|
| Product Or Component Type | Die-cast empty control station | |
| Device Short Name | XAPG | |
| Product Destination | For Ø 22 mm control and signalling units | |
| Number Of Cut-Out | 2 cut-outs | |
| Colour Of Base Of Enclosure | Grey RAL 7032) | |
| Colour Of Cover | Grey RAL 7032) | |
| Control Station Type | Metal | |
| Material | Die cast zinc | |
| Sale Per Indivisible Quantity | 1 | |
| Ip Degree Of Protection | IP65 IEC 60529 IP657 NF C 20-010 | |
| Resistance To Chemical Agents | Special treatment can be obtained on request | |

Complementary

| Number Of Vertical Rows | 2 | |
|---------------------------|--------------------------------|--|
| Number Of Horizontal Rows | 1 | |
| Cut-Out Dimensions | Ø 22 mm | |
| Cable Entry | cable gland 1 x cable gland | |
| Thread Type | 3/4 NPT | |
| Cad Overall Width | 3.15 in (80 mm) | |
| Cad Overall Height | 3.15 in (80 mm) | |
| Cad Overall Depth | 3.03 in (77 mm) | |
| Net Weight | 1.60 lb(US) (0.724 kg) | |
| Compatibility Code | XAPG | |

Environment

Protective Treatment TH

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Ambient Air Temperature For Storage | -40158 °F (-4070 °C) |
|---------------------------------------|--|
| Ambient Air Temperature For Operation | -13158 °F (-2570 °C) |
| Electrical Shock Protection Class | Class I IEC 60536 Class I NF C 20-030 |
| Ik Degree Of Protection | IK07 EN/IEC 62262 |

Ordering and shipping details

| Category | US10CS222475 | |
|-------------------|---------------|--|
| Discount Schedule | 0CS2 | |
| Gtin | 3389118381872 | |
| Returnability | No | |
| Country Of Origin | FR | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.91 in (15 cm) |
| Package 1 Width | 11.81 in (30 cm) |
| Package 1 Length | 15.75 in (40 cm) |
| Package 1 Weight | 21.16 oz (600 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ⊘ | Toxic Heavy Metal Free | |
| ⊘ | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |