

# Product data sheet

Specifications



Harmony XAP, Empty control station, zinc alloy, grey, undrilled, Ø22, 175 x 80 x 77 mm

XAPG39400

Discontinued on: Dec 2, 2020

End-of-service on: Dec 31, 2020

Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

## Main

Range Of Product	Harmony XAP
Product Or Component Type	Die-cast empty control station
Device Short Name	XAPG
Product Destination	For Ø 22 mm control and signalling units
Number Of Cut-Out	Undrilled
Colour Of Base Of Enclosure	Grey RAL 7032)
Colour Of Cover	Grey RAL 7032)
Control Station Type	Metal
Material	Die cast zinc
Sale Per Indivisible Quantity	1
Ip Degree Of Protection	IP65 IEC 60529
Resistance To Chemical Agents	Special treatment can be obtained on request

## Complementary

Number Of Vertical Rows	0
Number Of Horizontal Rows	0
Cut-Out Dimensions	Ø 22 mm
Cable Entry	cable gland 1 x cable gland
Thread Type	3/4 NPT
Cad Overall Width	3.15 in (80 mm)
Cad Overall Height	6.89 in (175 mm)
Cad Overall Depth	3.03 in (77 mm)
Net Weight	2.56 lb(US) (1.160 kg)
Compatibility Code	XAPG

## Environment

Protective Treatment	TH
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030
Ik Degree Of Protection	IK07 EN/IEC 62262

## Ordering and shipping details

Category	US10CS222475
Discount Schedule	0CS2
Gtin	3389118381773
Returnability	No
Country Of Origin	MA

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	4.72 in (12 cm)
Package 1 Length	7.32 in (18.6 cm)
Package 1 Weight	2.98 lb(US) (1.352 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



**Green Premium™** label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.





[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>