# Product data sheet

Specifications





## Die cast empty control station, Harmony XAP, zinc alloy, grey, 4 cut outs, 22mm, 175x80x51.5mm

XAPG39704

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 261.00 USD

### Main

Range Of Product	Harmony XAP	
Product Or Component Type	Die-cast empty control station	
Device Short Name	XAPG	
Product Destination	For Ø 22 mm control and signalling units	
Number Of Cut-Out	4 cut-outs	
Colour Of Base Of Enclosure	Grey RAL 7032)	
Colour Of Cover	Grey RAL 7032)	
Control Station Type	Metal	
Material	Die cast zinc	
Sale Per Indivisible Quantity	1	
Ip Degree Of Protection	IP65 IEC 60529	
Resistance To Chemical Agents	Special treatment can be obtained on request	

### Complementary

Number Of Vertical Rows	1	
Number Of Horizontal Rows	4	
Cut-Out Dimensions	Ø 22 mm	
Cable Entry	cable gland 1 x cable gland	
Thread Type	3/4 NPT	
Cad Overall Width	3.15 in (80 mm)	
Cad Overall Height	6.89 in (175 mm)	
Cad Overall Depth	2.03 in (51.5 mm)	
Net Weight	1.90 lb(US) (0.860 kg)	
Compatibility Code	XAPG	

### Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030
Ik Degree Of Protection	IK07 IEC 62262

## Ordering and shipping details

Category	US10CS222475	
Discount Schedule	0CS2	
Gtin	3389118381742	
Returnability	No	
Country Of Origin	US	

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.91 in (15.0 cm)	
Package 1 Width	11.81 in (30.0 cm)	
Package 1 Length	15.75 in (40.0 cm)	
Package 1 Weight	31.04 oz (880.0 g)	

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov