## Product data sheet

Specifications

 Green Premium"



# empty control station - XAP-J - metal - without opening

XAPJ34

() Discontinued on: Jun 30, 2022

(!) End-of-service on: Jul 28, 2022

() Discontinued

#### Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	ХАРЈ						
Product Front Plate Size	80 x 175 mm						
Usable Depth	2.93 in (74.5 mm)						
Number Of Cut-Out	Undrilled						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Yellow						
Material	Zinc alloy						
Cable Entry	1 hole with blanking plug for cable gland 0.55 in (14 mm) 1 hole without blanking plug for cable gland 0.55 in (14 mm)						
Product Mounting	Flush mounting						
Ip Degree Of Protection	IP65 IEC 60529						

#### Complementary

Net Weight

2.56 lb(US) (1.16 kg)

## Environment

Protective Treatment	тс					
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)					
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)					
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030					

## Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)				
Discount Schedule	CS2				
Gtin	3389110666144				
Returnability	No				

## **Packing Units**

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	4.72 in (12 cm)
Package 1 Length	7.48 in (19 cm)
Package 1 Weight	2.92 lb(US) (1.325 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration					
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Circularity Profile	No need of specific recycling operations					
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov					

## Product data sheet

#### **Dimensions Drawings**

#### **Dimensions and Fixing**



(1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity

(2) 1 hole, with blanking plug (protrusion 6 mm/0.24 in.), for cable gland with 18 mm/0.71 in. maximum clamping capacity

а		b		С		G		н		P	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	175	6.89	77	3.03	50	1.97	160	6.30	74.5	2.93

(3)  $2 \times \emptyset$  5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.