


# Product data sheet

Specifications



## die-cast empty control station - XAPJ - Ø 30.5 - zinc alloy - 2 openings

XAPJ3802H29

 **Discontinued on:** Dec 19, 2019

 **Discontinued**

### Main

Range Of Product	Harmony XAP
Product Or Component Type	Die-cast empty control station
Device Short Name	XAPJ
Product Destination	For Ø 30.5 mm control and signalling units
Product Front Plate Size	80 x 175 mm
Usable Depth	2.93 in (74.5 mm)
Number Of Cut-Out	2 cut-outs
Colour Of Base Of Enclosure	Blue
Colour Of Cover	Yellow
Material	Zinc alloy
Cable Entry	1 hole with blanking plug for ISO 429248 cable gland 0.98 in (25 mm) 1 hole without blanking plug for ISO 429248 cable gland 0.98 in (25 mm)
Device Mounting	Flush
Ip Degree Of Protection	IP65 IEC 60529 IP69 NF C 20-010 IP69K

### Complementary

Number Of Vertical Rows	1
-------------------------	---

### Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-40...158 °F (-40...70 °C)
Overvoltage Category	Class I IEC 60536 Class I NF C 20-030

### Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)
Discount Schedule	CS2
Gtin	3389118115637
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------