Product data sheet





Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, undrilled, 80 x 220 x 77 mm

XAPM44

! Discontinued on: Aug 30, 2022



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAP						
Product Or Component Type	Die-cast empty control station						
Device Short Name	XAPM						
Product Front Plate Size	80 x 220 mm						
Usable Depth	2.93 in (74.5 mm)						
Number Of Cut-Out	Undrilled						
Colour Of Base Of Enclosure	Blue						
Colour Of Cover	Blue						
Material	Zinc alloy						
Cable Entry	1 hole without blanking plug for cable gland 0.71 in (18 mm)						
Product Mounting	Flush mounting						
Ip Degree Of Protection	IP65 IEC 60529						

Complementary

Net Weight 3.11 lb(US) (1.41 kg)

Environment

Protective Treatment	TC					
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)					
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)					
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030					

Ordering and shipping details

Category	US10CS218406
Discount Schedule	0CS2
Gtin	3389110312720
Returnability	No
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	3.46 in (8.8 cm)				
Package 1 Width	5.12 in (13 cm)				
Package 1 Length	9.13 in (23.2 cm)				
Package 1 Weight	3.52 lb(US) (1.595 kg)				

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance


②	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

Dimensions Drawings

Dimensions and Fixing



- (1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity
- (3) $2 \times \emptyset$ 5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	220	8.66	77	3.03	50	1.97	205	8.07	74.5	2.93