# **Product data sheet**

Specifications





(!) Discontinued

Harmony XAP, XB2 SL, Empty control station, zinc alloy, blue, undrilled, with ISO cable entries, 80 x 220 x 77 mm

XAPM44H29

- Discontinued on: Jun 30, 2022
  - ! End-of-service on: Jul 28, 2022

### Main

Range Of Product	Harmony XAP							
Product Or Component Type	Die-cast empty control station							
Device Short Name	XAPM							
Product Front Plate Size	80 x 220 mm							
Usable Depth	2.93 in (74.5 mm)							
Number Of Cut-Out	Undrilled							
Colour Of Base Of Enclosure	Blue							
Colour Of Cover	Blue							
Material	Zinc alloy							
Cable Entry	1 hole without blanking plug for ISO 429248 cable gland 0.98 in (25 mm)							
Product Mounting	Flush mounting							
Ip Degree Of Protection	IP65 IEC 60529							

### Complementary

Net Weight 3.11 lb(US) (1.41 kg)

### **Environment**

Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030

### Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)				
Discount Schedule	CS2				
Gtin	3389110891300				
Returnability	No				
Country Of Origin	MA				

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE				
Number Of Units In Package 1	1				
Package 1 Height	5.16 in (13.1 cm)				
Package 1 Width	3.46 in (8.8 cm)				
Package 1 Length	9.13 in (23.2 cm)				
Package 1 Weight	3.55 lb(US) (1.61 kg)				

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance


<b>Ø</b>	Reach Free Of Svhc	
<b>②</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration						
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration						
China Rohs Regulation	China RoHS declaration						
Environmental Disclosure	Product Environmental Profile						
Circularity Profile	No need of specific recycling operations						
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov						

### **Dimensions Drawings**

### **Dimensions and Fixing**



- (1) 1 hole, without blanking plug, for cable gland with 18 mm/0.71 in. maximum clamping capacity
- (3)  $2 \times \emptyset$  5.6 mm/0.22 in. holes, depth 20 mm/0.79 in.

а		b		С		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	220	8.66	77	3.03	50	1.97	205	8.07	74.5	2.93