# Product data sheet

Specifications



# Harmony XAP, XB2 SL, Empty control station, aluminium, blue, undrilled, with ISO cable entries, 85 x 310 x 77 mm

XAF	PM54H29
!	Discontinued on: Jun 30, 2022

() End-of-service on: Jul 28, 2022

#### Main

Range Of Product	Harmony XAP					
Product Or Component Type	Die-cast empty control station					
Device Short Name	ХАРМ					
Product Front Plate Size	85 x 310 mm					
Usable Depth	2.93 in (74.5 mm)					
Number Of Cut-Out	Undrilled					
Colour Of Base Of Enclosure	Blue					
Colour Of Cover	Blue					
Material	Aluminium alloy					
Cable Entry	1 hole without blanking plug for ISO 429248 cable gland 1.26 in (32 mm)					
Product Mounting	Flush mounting					
Ip Degree Of Protection	IP65 IEC 60529					

#### Complementary

 Net Weight
 1.87 lb(US) (0.85 kg)

#### Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I IEC 60536 Class I NF C 20-030

#### Ordering and shipping details

Category	18406-WORLD SERVICE PARTS(OTHER OP INT)				
Discount Schedule	CS2				
Gtin	3389118115316				
Returnability	No				
Country Of Origin	FR				

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE			
Number Of Units In Package 1	1			
Package 1 Height	4.80 in (12.2 cm)			
Package 1 Width	3.54 in (9 cm)			
Package 1 Length	12.40 in (31.5 cm)			
Package 1 Weight	34.84 oz (987.667 g)			

#### **Contractual warranty**

Warranty

18 months

### Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
 Toxic Heavy Metal Free
 Mercury Free
 Rohs Exemption Information Yes


#### **Certifications & Standards**

Reach Regulation	REACh Declaration				
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration				
China Rohs Regulation	China RoHS declaration				
Environmental Disclosure	Product Environmental Profile				
Circularity Profile	No need of specific recycling operations				
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov				

#### Product data sheet

#### **Dimensions Drawings**

#### **Dimensions and Fixing**



- (1) 1 hole, without blanking plug, for cable gland with 24 mm/0.94 in. maximum clamping capacity
- (3)  $2 \times \emptyset 5.6 \text{ mm}/0.22 \text{ in. holes, depth } 20 \text{ mm}/0.79 \text{ in.}$

а		b		с		G		Н		Р	
mm	in.	mm	in.	mm	in.	mm	in.	mm	in.	mm	in.
80	3.15	310	12.20	77	3.03	50	1.97	295	11.61	74.5	2.93