

Product data sheet

Specifications

yellow pushbutton Ø 22 - flush
spring return - 1NO



XB2BA51

⚠ Discontinued on: Jul 5, 2023

⚠ Discontinued

Main

Product Or Component Type	Complete push-button
Device Short Name	XB2B
Bezel Material	Chromium plated metal
Mounting Diameter	0.87 in (22 mm)
Sale Per Indivisible Quantity	1

Complementary

Shape Of Signaling Unit Head	Round
Height	1.85 in (47 mm)
Width	1.18 in (30 mm)
Depth	2.05 in (52 mm)

Environment

Protective Treatment	TC
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature For Operation	-13...131 °F (-25...55 °C)

Ordering and shipping details

Category	22461-PUSHBUTTON, 22MM_(METAL)
Discount Schedule	CS2
Gtin	3389110610253
Returnability	No
Country Of Origin	ES

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.30 in (3.3 cm)
Package 1 Width	1.69 in (4.3 cm)
Package 1 Length	2.28 in (5.8 cm)
Package 1 Weight	2.50 oz (71.0 g)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	CAR
Number Of Units In Package 2	1
Package 2 Height	1.30 in (3.3 cm)
Package 2 Width	1.69 in (4.3 cm)
Package 2 Length	2.28 in (5.8 cm)
Package 2 Weight	2.50 oz (71.0 g)
Unit Type Of Package 3	BB1
Number Of Units In Package 3	10
Package 3 Height	3.43 in (8.7 cm)
Package 3 Width	6.69 in (17.0 cm)
Package 3 Length	39.37 in (100.0 cm)
Package 3 Weight	25.36 oz (719.0 g)

Contractual warranty

Warranty	18 months
----------	-----------