Product data sheet

Specifications





Annunciator, Harmony XB5, Complete buzzer, plastic, 22mm, continuous or intermittent tone, 230...240V AC

XB5KSM



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XB5
Product Or Component Type	Annunciator
Bezel Material	Dark grey plastic
Mounting Diameter	0.87 in (22 mm)
Head Type	Standard
Cap/Operator Or Lens Colour	Black

Complementary

Supply Circuit Type	AC
Supply Frequency	50 Hz
Signalling Type	Continuous or intermittent tone
Noise Level	90 dB 6.8 kHz 0.1 m +/- 10 %
Resistance To High Pressure Washer	1305.34 psi (9000000 Pa) 176 °F (80 °C) 0.1 m
Height	1.14 in (29 mm)
Width	1.14 in (29 mm)
Depth	2.17 in (55 mm)
Net Weight	0.05 lb(US) (0.024 kg)
Current Consumption	<= 18 mA
[Us] Rated Supply Voltage	230240 V +/- 10 %

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Overvoltage Category	Class II IEC 60536
Electrical Shock Protection Class	Class II IEC 60536
Nema Degree Of Protection	NEMA 4X NEMA 13

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	IEC 60947-5-1
	IEC 60947-5-4
	UL 508
	JIS C8201-5-1
	IEC 60947-5-1
	IEC 60947-1
	CSA C22.2 No 14
	IEC 60947-5-4
	IEC 60947-1
	JIS C8201-1
	IEC 60529
	IEC 62262
	IEC 50102
Product Certifications	UL Listed
	CSA
	BV

Ordering and shipping details

Category	US10CS222467
Discount Schedule	0CS2
Gtin	3389110102697
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.34 in (3.4 cm)
Package 1 Width	1.34 in (3.4 cm)
Package 1 Length	2.24 in (5.7 cm)
Package 1 Weight	0.99 oz (28.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	88
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.99 lb(US) (2.715 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

Dimensions Drawings

Dimensions



e: Clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.


Product data sheet

XB5KSM

Mounting and Clearance

Panel Cut-out for Buzzer

Connection by Screw Clamp Terminals




(1) Diameter on finished panel or support (2) Ø22.5 mm recommended (Ø22.3 $_0^{+0.4}$) / Ø0.89 in. recommended (Ø0.88 in. $_0^{+0.016}$)


Connections	a in mm	a in in.	b in mm	b in in.
By screw clamp terminals or plug-in connector	40	1.57	30	1.18

XB5KSM

Connections and Schema

Cabling of Annunciators





- (1) Supply(2) Intermittent(3) Continuous