Product data sheet

Specification





Selector switch, Harmony XB6, black round, 16mm, 3 positions, stay put, 1NO + 1NC

XB6AD235B

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 37.60 USD

Main

Range Of Product	Harmony XB6	
Product Or Component Type	Complete selector switch	
Device Short Name	XB6	
Bezel Material	Plastic	
Mounting Diameter	0.63 in (16 mm)	
Sale Per Indivisible Quantity	1	
Operating Position	Any position	
Shape Of Signaling Unit Head	Square	
Type Of Operator	stay put	
Operator Profile	Black standard handle	
Operator Position Information	3 positions 60°	
Contacts Type And Composition	2 NO	
Contact Operation	Slow-break	

Complementary

Height	0.71 in (18 mm)	
Width	0.71 in (18 mm)	
Depth	2.68 in (68 mm)	
Terminals Description Iso N°1	(21-22)NC (13-14)NO	
Net Weight	0.05 lb(US) (0.024 kg)	
Positive Opening	With IEC 60947-5-1 appendix K	
Mechanical Durability	500000 cycles	
Connections - Terminals	Faston connectors 2.8 x 0.5 mm	
Contacts Material	Silver alloy (Ag/Ni)	
Short-Circuit Protection	6 A cartridge fuse gG	
[Ui] Rated Insulation Voltage	250 V 3)IEC 60947-1	
[Uimp] Rated Impulse Withstand Voltage	d 4 kV IEC 60947-1	
[le] Rated Operational Current	3 A 120 V, AC-15, B300 IEC 60947-5-1 1.5 A 240 V, AC-15, B300 IEC 60947-5-1 0.1 A 250 V, DC-13, R300 IEC 60947-5-1	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

0.22 A 125 V, DC-13, R300 IEC 60947-5-1

Electrical Durability	1000000 cycles, AC-15 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C 1000000 cycles, DC-13 230 V 3600 cyc/h 0.5 IEC 60947-5-1 appendix C
Electrical Reliability	Λ = 10exp(-8) 5 V 1 mA with confidence level of 90 % IEC 60947-5-4

Environment

Protective Treatment	тс
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class II IEC 61140
Ip Degree Of Protection IP65 IEC 60529	
Nema Degree Of Protection	NEMA 13 UL 50 NEMA 4 UL 50 NEMA 4X UL 50 NEMA 13 CSA C22.2 No 94 NEMA 4 CSA C22.2 No 94 NEMA 4X CSA C22.2 No 94
Standards	UL 508 CSA C22.2 No 14 IEC 60947-1 JIS C8201-5-1 IEC 60947-5-1 IEC 60947-5-5 JIS C 852 JIS C8201-1
Product Certifications	GOST UL CCC CSA
Vibration Resistance	+/- 3 mm 2500 Hz)IEC 60068-2-6 5 gn 2500 Hz)IEC 60068-2-6
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	US10CS222459	
Discount Schedule	0CS2	
Gtin	3389110764611	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.0 cm)
Package 1 Width	4.33 in (11.0 cm)
Package 1 Length	6.30 in (16.0 cm)
Package 1 Weight	0.56 oz (16.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	60
Package 2 Height	5.91 in (15.0 cm)

Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	2.52 lb(US) (1.141 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
Ø	Toxic Heavy Metal Free	
Ø	Mercury Free	
9	Rohs Exemption Information	Yes


Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Circular Head Selector Switch, Standard Handle

Dimensions



e panel thickness 1 to 6 mm/0.03 to 0.23 in.

XB6AD235B

Mounting and Clearance

Panel Cut-out

For Square or Circular Head

