

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 296.00 USD



### Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRT
Movement of operating head	Rotary
Type of operator	Roller lever stainless steel
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Associated complete product	XCRT315
-----------------------------	---------

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
---------------------------------------	----------------------------

### Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	003389110606201
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5300000000000003
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1103 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------