Specifications





Indicating Bank, 70mm, base unit and cap, direct or tube mounting, bottom or side cable entry

XVBC21

Product availability: Stock - Normally stocked in distribution facility

Price*: 61.00 USD

Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Base unit with cover
Component Name	XVBC
Material	Glass reinforced polyamide: base unit Polycarbonate: cover unit

Complementary

Direct or tube fixing
2.76 in (70 mm)
Banks without flash discharge tube unit
1 connector standard input
Bottom or side entry
Customer assembly, up to 5 units
(GND)GROUND (COM-1)PW (COM-4)PW (COM-3)PW (COM-5)PW (COM-2)PW
0.42 lb(US) (0.19 kg)

Environment

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	IEC 60947-5-1
Protective Treatment	ТС
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Nema Degree Of Protection	Type 4X UL indoor)

Ordering and shipping details

Category	US100XV22611	
Discount Schedule	00XV	
Gtin	3389110845020	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Returnability	Yes
Country Of Origin	US

Packing Units

PCE
1
3.35 in (8.500 cm)
3.94 in (10.000 cm)
3.74 in (9.500 cm)
7.27 oz (206.000 g)
S03
36
11.81 in (30.000 cm)
11.81 in (30.000 cm)
15.75 in (40.000 cm)
18.02 lb(US) (8.173 kg)
P06
288
29.53 in (75.000 cm)
23.62 in (60.000 cm)
31.50 in (80.000 cm)
157.67 lb(US) (71.516 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards


Reach Regulation	REACh Declaration			
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)			
China Rohs Regulation	China RoHS declaration			
Environmental Disclosure	Product Environmental Profile			
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.			
Circularity Profile	No need of specific recycling operations			
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov			

Dimensions Drawings

Indicator Bank without "Flash" Discharge Tube Unit

Dimensions

Below drawing shows the minimum configuration of the product. Select the number of stages according to the product characteristics in order to get \mathbf{b} dimension.




- (1) Base unit
- (2) Illuminated or audible signalling unit XVBC ..., to be ordered separately
- (3) Cover (supplied with base unit)

Number of illuminated or audible signalling units (no "flash")	b in mm	b in in.
1	138	5.43
2	201	7.91
3	264	10.39
4	327	12.87
5	390	15.35

Mounting and Clearance

Base Unit for Indicator Banks

Panel Cut-out for Direct Fixing



Connections and Schema

Illuminated Beacon

Wiring Diagram

