# **Product data sheet**

Specifications





# Complete beacon, Harmony XVB Universal, indicating 48 VDC 10 W +options

XVBL4B7

! Discontinued on: Dec 2, 2020

! End-of-service on: Dec 31, 2020

#### ① Discontinued

#### Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Complete beacon
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit
Signalling Type	Flashing
Mounting Diameter	2.76 in (70 mm)
Component Name	XVBL
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, clear
Bulb Type	Incandescent Incandescent BA 15d Protected LED
[Us] Rated Supply Voltage	24 V AC 2448 V DC
Maximum Power Dissipation In W	7 W

## Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V IEC 60947-1
Nominal Voltage Limit	0.851.1 Un IEC 60947-5-1
[Uimp] Rated Impulse Withstand Voltage	4 kV IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	5.47 in (139 mm)
Cad Overall Depth	2.76 in (70 mm)
Terminals Description Iso N°1	(COM-1)PW (GND)GROUND
Net Weight	0.62 lb(US) (0.28 kg)

#### **Environment**

Pollution Degree

2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
Nema Degree Of Protection	Type 4X UL indoor)

# Ordering and shipping details

Category	22611-XVB-STACKLIGHTS
Discount Schedule	XV
Gtin	3389110844221
Returnability	No
Country Of Origin	CZ

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.71 in (14.5 cm)
Package 1 Width	3.15 in (8 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	9.88 oz (280 g)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

#### XVBL4B7

#### **Dimensions Drawings**

#### Illuminated Beacon for BA 15d Bulb or LED

#### **Dimensions**



## **Product data sheet**

#### XVBL4B7

Connections and Schema

#### Illuminated Beacon

#### Wiring Diagram

