Product data sheet

Specifications





Complete beacon, Harmony XVB Universal, indicating 48 VDC 10 W +options

XVBL4B8

! Discontinued on: Oct 9, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XVB Universal
Product Or Component Type	Complete beacon
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit
Signalling Type	Flashing
Mounting Diameter	2.76 in (70 mm)
Component Name	XVBL
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit
Light Source	Bulb not included, yellow
Bulb Type	Incandescent Incandescent BA 15d Protected LED
[Us] Rated Supply Voltage	24 V AC 2448 V DC
Maximum Power Dissipation In W	7 W

Complementary

•	
Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm² with cable end
[Ui] Rated Insulation Voltage	250 V IEC 60947-1
Nominal Voltage Limit	0.851.1 Un IEC 60947-5-1
[Uimp] Rated Impulse Withstand Voltage	4 kV IEC 60947-1
Flashing Frequency	1 Hz
Cad Overall Width	2.76 in (70 mm)
Cad Overall Height	5.47 in (139 mm)
Cad Overall Depth	2.76 in (70 mm)
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW
Net Weight	0.62 lb(US) (0.28 kg)

Environment

Pollution Degree

2

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508
Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Electrical Shock Protection Class	Class I on support tube IEC 61140 Class II on base unit IEC 61140
Ip Degree Of Protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529
Nema Degree Of Protection	Type 4X UL indoor)

Ordering and shipping details

Category	US100XV22611
Discount Schedule	00XV
Gtin	3389110844238
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.15 in (8.0 cm)
Package 1 Width	3.15 in (8.0 cm)
Package 1 Length	5.71 in (14.5 cm)
Package 1 Weight	9.66 oz (274.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	18
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	11.90 lb(US) (5.4 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

XVBL4B8

Dimensions Drawings

Illuminated Beacon for BA 15d Bulb or LED

Dimensions



Product data sheet

XVBL4B8

Connections and Schema

Illuminated Beacon

Wiring Diagram

