Product data sheet

Specifications





Complete beacon, Harmony XVB Universal, blue strobe beacon, 70mm, 5 joules, 24V AC/DC

XVBL6B6

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 427.50 USD

Main

Range Of Product	Harmony XVB Universal	
Product Or Component Type	Complete beacon	
Beacon Or Indicator Bank Unit Type	Base unit direct or tube fixing Illuminated unit	
Signalling Type	Flashing	
Mounting Diameter	2.76 in (70 mm)	
Component Name	XVBL	
Material	Glass reinforced polyamide: base unit Polycarbonate: illuminated unit	
Light Source	Integral flash discharge tube, blue	
Bulb Type	Flash discharge tube	
[Us] Rated Supply Voltage	24 V AC/DC	

Complementary

Connections - Terminals	Screw clamp terminals, <= 1 x 1.5 mm ² with cable end	
[Ui] Rated Insulation Voltage	250 V IEC 60947-1	
Nominal Voltage Limit	0.851.1 Un IEC 60947-5-1	
Current Consumption	< 350 mA DC < 550 mA AC	
[Uimp] Rated Impulse Withstand Voltage	4 KV IEC 60947-1	
Flash Energy	5 J	
Flashing Frequency	1 Hz	
Cad Overall Width	2.76 in (70 mm)	
Cad Overall Height	9.13 in (232 mm)	
Cad Overall Depth	2.76 in (70 mm)	
Terminals Description Iso N°1	(GND)GROUND (COM-1)PW	
Net Weight	0.97 lb(US) (0.44 kg)	

Environment

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Product Certifications	CCC EAC CSA C22-2 No 14 UL 508	
Standards	IEC 60947-5-1	
Protective Treatment	тс	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Electrical Shock Protection Class	Class I on support tube IEC 61140 Class II on base unit IEC 61140	
Ip Degree Of Protection	IP65 on fixing base XVBZ0. IEC 60529 IP66 on base unit IEC 60529	
Nema Degree Of Protection	Type 4X UL indoor)	

Ordering and shipping details

Category	US100XV22611	
Discount Schedule	00XV	
Gtin	3389110844696	
Returnability	No	
Country Of Origin	CZ	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.74 in (9.5 cm)
Package 1 Width	10.24 in (26.0 cm)
Package 1 Length	3.74 in (9.5 cm)
Package 1 Weight	15.52 oz (440.0 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	12.67 lb(US) (5.746 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information
Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Product data sheet

Dimensions Drawings

Illuminated Beacon with "Flash" Discharge Tube Unit

Dimensions



Product data sheet

Connections and Schema

Illuminated Beacon

Wiring Diagram

