

# Product data sheet

## Characteristics

# XZCRV1512040A1

jumper cable XZ - male straight M12 3-pin - female elbowed M12 3-pin - PVC 1m

Product availability : Non-Stock - Not normally stocked in distribution facility

Price\* : 27.00 USD



### Main

|                                    |                   |
|------------------------------------|-------------------|
| Accessory / separate part category | Cabling accessory |
| Accessory / separate part type     | Jumper cable      |

### Complementary

|                             |   |
|-----------------------------|---|
| Jumper cable end 1          | M12 male, :3 pins (straight), fixing: screw-on  |
| Jumper cable end 2          | M12 female, :3 pins (elbowed), fixing: screw-on |
| Collar material             | Metal   |
| Cable composition           | 3 x 0.25 mm <sup>2</sup>                        |
| Cable length                | 3.28 ft (1 m)                                   |
| Wire insulation material    | PVC   |
| Cable outer diameter        | 0.18 in (4.6 mm)                                |
| System Voltage              | 250 V AC<br>300 V DC                            |
| Line Rated Current          | 3 A   |
| Insulation resistance       | >= 1000 MOhm                                    |
| Resistance across terminals | <= 5000 mOhm                                    |
| Product weight              | 0.15 lb(US) (0.07 kg)                           |

### Environment


|                                       |                                     |
|---------------------------------------|-------------------------------------|
| IP degree of protection               | IP65<br>IP67                        |
| Product certifications                | CULus                               |
| Ambient air temperature for operation | -13...176 °F (-25...80 °C) (static) |
| Ambient air temperature for storage   | -13...176 °F (-25...80 °C)          |

### Ordering and shipping details

|                       |                        |
|-----------------------|------------------------|
| Category              | 22483 - MACHINE CABLES |
| Discount Schedule     | DS3                    |
| GTIN                  | 00785901716624         |
| Nbr. of units in pkg. | 1                      |

|                     |      |
|---------------------|------|
| Package weight(Lbs) | 0.12 |
| Returnability       | N    |
| Country of origin   | PL   |

**Offer Sustainability**

|                           |   |
|---------------------------|---|
| RoHS (date code: YYWW)    | Compliant - since 1201 - Schneider Electric declaration of conformity<br> <a href="#">Schneider Electric declaration of conformity</a> |
| California proposition 65 | WARNING: This product can expose you to chemicals including:  |
| ----- Substance 1         | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and   |
| ----- Substance 2         | Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.  |
| ----- More information    | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>   |

**Contractual warranty**

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|