

Product data sheet

Specifications



cap - pushbutton head - Ø 22 mm - green - I

ZA2BA331

⚠ Discontinued on: Jan 29, 2021

⚠ Discontinued

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACA

Complementary

Marking	Unmarked
Cap/Operator Or Lens Colour	Green
Product Compatibility	XACA..
Mounting Location	Front of enclosure
Sale Per Indivisible Quantity	1
Standards	CSA C22.2 No 14 UL 508 EN/IEC 60947-5-1 EN/IEC 60204-32
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102
Net Weight	0.04 lb(US) (0.02 kg)

Ordering and shipping details

Category	22460-PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
Gtin	3389110648027
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	1.18 in (3 cm)
Package 1 Width	1.18 in (3 cm)
Package 1 Length	1.18 in (3 cm)
Package 1 Weight	0.53 oz (15 g)

Contractual warranty

Warranty	18 months
----------	-----------