

Product data sheet

Characteristics

ZA2BD2

black selector switch - 2 positions - standard handle

Product availability : Stock - Normally stocked in distribution facility

Price* : 30.00 USD



Main

Range of product	Harmony XAC
Product or component type	Selector switch
Component name	ZA2
Product compatibility	XACA

Complementary

Marking	Unmarked
Cap/Operator or lens colour	Black
Mounting location	Front of enclosure Base of enclosure
Sale per indivisible quantity	1
Product weight	0.04 lb(US) (0.018 kg)

Environment

Standards	EN/IEC 60204-32 EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	100 gn conforming to IEC 60068-2-27
Overvoltage category	Class II conforming to IEC 61140
IP degree of protection	IP65 conforming to IEC 60529
IK degree of protection	IK08 conforming to EN 50102

Ordering and shipping details

Category	22460 - PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	00785901645306

Nbr. of units in pkg.	1
Package weight(Lbs)	4.0000000000000001E-2
Returnability	Y
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

ZA2BD2 is replaced by:



Heads ZB5AD2
 black selector switch head Ø22 2-position stay put
 Qty 1
 Reason for Substitution: End of life | Substitution date: 01 January 2017