Product data sheet

Specifications





() Discontinued

Head for push button, Harmony XAC, black, booted, 22mm, unmarked

ZA2BP2

Product availability: Stock - Normally stocked in distribution facility

Main

Range Of Product	Harmony XAC	
Product Or Component Type	Head for push-button	
Component Name	XACA	

Complementary

complementary	
Marking	Unmarked
Operator Additional Information	Booted
Cap/Operator Or Lens Colour	Black
Product Compatibility	XACA
Mounting Location	Front of enclosure
Sale Per Indivisible Quantity	1
Standards	UL 508 CSA C22.2 No 14 EN/IEC 60947-5-1 EN/IEC 60204-32
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Overvoltage Category	Class II IEC 61140
Ip Degree Of Protection	IP65 conforming to IEC 60529
Ik Degree Of Protection	IK08 conforming to EN 50102
Net Weight	0.06 lb(US) (0.025 kg)

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
Gtin	3389110647969
Returnability	Yes
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.36 in (6.000 cm)
Package 1 Width	1.18 in (3.000 cm)
Package 1 Length	2.36 in (6.000 cm)
Package 1 Weight	0.56 oz (16.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	1.97 in (5.000 cm)
Package 2 Width	6.30 in (16.000 cm)
Package 2 Length	7.87 in (20.000 cm)
Package 2 Weight	5.82 oz (165.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.32 lb(US) (1.960 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov