Product data sheet

Specifications





pushbutton head - Ø 22 - red - booted - unmarked

ZA2BP4

Discontinued on: Jun 30, 2023

① Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range Of Product	Harmony XAC
Product Or Component Type	Head for push-button
Component Name	XACA

Complementary

Marking	Unmarked	
Operator Additional Information	Booted	
Cap/Operator Or Lens Colour	Red	
Product Compatibility	XACA	
Mounting Location	Front of enclosure	
Sale Per Indivisible Quantity	Indivisible Quantity 1	
Standards	IEC 60947-5-1 UL 508 IEC 60204-32 CSA C22.2 No 14	
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)	
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)	
Vibration Resistance	15 gn 10500 Hz)IEC 60068-2-6	
Shock Resistance	tance 100 gn IEC 60068-2-27	
Overvoltage Category	ory Class II IEC 61140	
Ip Degree Of Protection	IP65 conforming to IEC 60529	
Ik Degree Of Protection	etion IK08 conforming to IEC 62262	
Net Weight	0.06 lb(US) (0.025 kg)	

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
Gtin	3389110648003
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.18 in (3.0 cm)
Package 1 Length	1.38 in (3.5 cm)
Package 1 Weight	0.63 oz (18.0 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	2.36 in (6.0 cm)
Package 2 Width	5.51 in (14.0 cm)
Package 2 Length	6.30 in (16.0 cm)
Package 2 Weight	6.38 oz (181.0 g)
Unit Type Of Package 3	S01
Number Of Units In Package 3	100
Package 3 Height	5.91 in (15.0 cm)
Package 3 Width	5.91 in (15.0 cm)
Package 3 Length	15.75 in (40.0 cm)
Package 3 Weight	4.44 lb(US) (2.014 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov