

# Product data sheet

Specifications



## illuminated flush pushbutton head - Ø 22 - white

ZA2BW31

 **Discontinued on:** Jan 29, 2021

 **Discontinued**

### Main

Range Of Product	Harmony
Product Or Component Type	Head for illuminated push-button
Bezel Material	Plastic
Component Name	ZA2B
Shape Of Signaling Unit Head	Round
Electrical Circuit Type	Control circuit
Type Of Operator	Spring return

### Complementary

Mechanical Durability	3000000 cycles
Height	1.18 in (30 mm)
Width	1.18 in (30 mm)
Net Weight	0.03 lb(US) (0.013 kg)
Cap/Operator Or Lens Colour	White
Marking	Unmarked

### Environment

Ambient Air Temperature For Operation	-13...131 °F (-25...55 °C)
Ambient Air Temperature For Storage	-40...158 °F (-40...70 °C)
Vibration Resistance	15 gn 40...500 Hz)IEC 60068-2-6
Overvoltage Category	Class II IEC 60536 Class II NF C 20-030
Protective Treatment	TC/TH
Standards	VDE 0660-200 NF C 63-140 IEC 60337-1 EN/IEC 60947-5-1

### Ordering and shipping details

Category	22460-PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
Gtin	00785901264026

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	FR

### Contractual warranty

Warranty	18 months
----------	-----------