

Product data sheet

Specifications



Digital display head, Harmony XB5, 22mm, plastic, green, 7 segments LED + decimal point, 24V DC

ZA2VA03

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 178.00 USD

Main

Range Of Product	Harmony
Product Or Component Type	Digital display head
Mounting Diameter	0.87 in (22 mm)
Cap/Operator Or Lens Colour	Green
[Us] Rated Supply Voltage	24 V DC

Complementary

Display Type	7 segments LED + decimal point
Supply Voltage Limits	13...30 V
Net Weight	0.04 lb(US) (0.02 kg)

Environment

Product Certifications	UL CSA
Ambient Air Temperature For Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature For Storage	-40...185 °F (-40...85 °C)
Vibration Resistance	10 gn 10...500 Hz)IEC 60068-2-6
Shock Resistance	180 gn 11 ms IEC 60068-2-27
Electrical Shock Protection Class	Class II NF C 20-030
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
Gtin	3389110648935
Returnability	No
Country Of Origin	FR

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	1.65 in (4.2 cm)
Package 1 Weight	0.74 oz (21.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	28.32 oz (803.0 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov