# **Product data sheet**

Specification





# Digital display body, Harmony XB5, 22mm, BCD +decimal, 24V DC

ZA2VA11

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 588.00 USD

### Main

Range Of Product	Harmony
Product Or Component Type	Digital display body
[Us] Rated Supply Voltage	24 V DC
Connections - Terminals	Screw connectors, 0.5 x 2.5 mm <sup>2</sup>

## Complementary

Mounting Support	panel
Device Mounting	Fixing hole 0.88 in (22.3 mm)
Electronic Decoding	Decimal + BCD
Supply Voltage Limits	1330 V
Current Consumption	<= 36 mA 30 V <= 40 mA 24 V
Protection Type	Reverse polarity protection
Logic Input	Positive
Voltage State 0 Guaranteed	-305 V
Voltage State 1 Guaranteed	1330 V
Current State 0 Guaranteed	<= 1.4 mA
Current State 1 Guaranteed	49.5 mA
Net Weight	0.13 lb(US) (0.057 kg)

#### **Environment**

Product Certifications	UL CSA
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-40185 °F (-4085 °C)
Vibration Resistance	10 gn 10500 Hz)IEC 60068-2-6
Shock Resistance	180 gn 11 ms IEC 60068-2-27
Electrical Shock Protection Class	Class II IEC 60536 Class II NF C 20-030
Ip Degree Of Protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Ordering and shipping details

Category	US10CS222460
Discount Schedule	0CS2
Gtin	3389110648966
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.18 in (3.0 cm)
Package 1 Width	1.65 in (4.2 cm)
Package 1 Length	4.25 in (10.8 cm)
Package 1 Weight	2.01 oz (57.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	30
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	4.23 lb(US) (1.917 kg)

## **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
<b>Environmental Disclosure</b>	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·