

Price\* : 644.00 USD

ZA2VA12 has not been replaced. Please contact your customer care center for more information.



ⓘ Discontinued

### Main

Range of product	Harmony
Product or component type	Digital display body
[Us] rated supply voltage	24 V DC
Connections - terminals	Screw connectors: 0.5 x 2.5 mm <sup>2</sup>

### Complementary

Mounting support	Panel
Device mounting	Fixing hole: Ø 0.88 in (22.3 mm)
Electronic decoding	BCD + latch
Supply voltage limits	13...30 V
Current consumption	<= 36 mA at 30 V <= 40 mA at 24 V
Protection type	Reverse polarity protection
Logic input	Positive
Voltage state 0 guaranteed	-30...5 V
Voltage state 1 guaranteed	13...30 V
Current state 0 guaranteed	<= 1.4 mA
Current state 1 guaranteed	4...9.5 mA

### Environment

Product certifications	CSA UL
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Vibration resistance	10 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
Shock resistance	180 gn 11 ms conforming to IEC 60068-2-27
Electrical shock protection class	Class II conforming to NF C 20-030 Class II conforming to IEC 60536
IP degree of protection	IP65 conforming to IEC 60529 IP65 conforming to NF C 20-010

Ordering and shipping details

Category	22460 - PUSHBUTTONS 22MM (PLASTIC)
Discount Schedule	CS2
GTIN	00785901248781
Nbr. of units in pkg.	1
Package weight(Lbs)	0.13
Returnability	N
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------