

# Product data sheet

Specifications



Remote control, Harmony eXLhoist, standard, display, 6 motion push buttons, 2 auxiliary push buttons

ZART8D

Product availability: Stock - Normally stocked in distribution facility

Price\*: 648.00 USD

## Main

Range Of Product	Harmony eXLhoist
Product Or Component Type	Hand-held remote control
Device Short Name	ZART
Control Button Type	6 configurable motion push-button 2 configurable auxiliary push-button

## Complementary

Material	Enclosure PC (polycarbonate) Enclosure PBT (polybutylene terephthalate) Cover PP (polypropylene) Protective cover EPDM rubber
Function Available	Accelerometer function Vibrator function
Display Type	LCD display 34 x 42 mm
Operating Distance	50 m
Mechanical Robustness	Free fall resistance 4.5 m IEC 60068-2-27
Communication Network Type	Wireless bluetooth low energy
Transmission Frequency	2.4 GHz
Maximum Sensing Distance	328.08 ft (100 m) in free field
Response Time	< 300 ms full duplex
Charging Time	900 s
Autonomy	30 h
Mechanical Durability	5000000 cycles
Service Life	5 year(s)
Width	3.94 in (100 mm)
Height	13.39 in (340 mm)
Depth	3.54 in (90 mm)
Net Weight	1.43 lb(US) (0.65 kg)

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Radio Agreement	ANATEL ICASA SRRRC FCC ARIB RSS
Ip Degree Of Protection	IP65
Nema Degree Of Protection	NEMA 4
Ambient Air Temperature For Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature For Storage	-4...113 °F (-20...45 °C)
Operating Altitude	0...6561.68 ft (0...2000 m)
Storage Altitude	0.00...9842.52 ft (0...3000 m)
Vibration Resistance	0.075 mm 10...55 Hz)IEC 60068-2-6
Shock Resistance	100 gn IEC 60068-2-27
Relative Humidity	0...95 % -4...140 °F (-20...60 °C) operating
Product Certifications	CE UL JIS EAC C-tick CSA KC

## Ordering and shipping details

Category	US10CS222479
Discount Schedule	0CS2
Gtin	3606480610363
Returnability	Yes
Country Of Origin	FR

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.21 in (10.7 cm)
Package 1 Width	4.13 in (10.5 cm)
Package 1 Length	13.23 in (33.6 cm)
Package 1 Weight	25.82 oz (732 g)
Unit Type Of Package 2	S03
Number Of Units In Package 2	4
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	7.57 lb(US) (3.432 kg)
Unit Type Of Package 3	P06
Number Of Units In Package 3	32
Package 3 Height	30.31 in (77 cm)

Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	77.17 lb(US) (35.004 kg)

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation

[China RoHS declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

Dimensions Drawings

Dimensions

