Product data sheet





green flush/red flush doubleheaded pushbutton Ø22 with marking

ZB4BA9234

! Discontinued on: Jan 23, 2021



Main

Range Of Product	Harmony XB4	
Product Or Component Type	Head for double-headed push-button	
Device Short Name	ZB4	
Bezel Material	Chromium plated metal	
Mounting Diameter	0.87 in (22 mm)	
Sale Per Indivisible Quantity 1		
Shape Of Signaling Unit Head	Rectangular	
Type Of Operator	spring return	
Operator Profile	2 flush push-buttons	
Operators Description	Green "I" - red "O"	

Complementary

Cad Overall Width	1.18 in (30 mm)
Cad Overall Height	1.97 in (50 mm)
Cad Overall Depth	1.38 in (35 mm)
Net Weight	0.11 lb(US) (0.052 kg)
Resistance To High Pressure Washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
Colour Of Marking	White marking when green, red or black caps Black marking when white caps
Operator Profile	Green flush, I white) Red flush, O white)
Mechanical Durability	1000000 cycles

Environment

Protective Treatment	тн
Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Electrical Shock Protection Class	Class I IEC 60536
Ip Degree Of Protection	IP66 IEC 60529
Nema Degree Of Protection	NEMA 13 NEMA 4X
Ik Degree Of Protection	IK03 conforming to IEC 50102

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	EN/IEC 60947-5-1 EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-4 JIS C8201-5-1 UL 508 EN/IEC 60947-5-5 JIS C8201-1	
Product Certifications	LROS (Lloyds register of shipping) BV DNV GL UL Listed CSA	
Vibration Resistance	5 gn 2500 Hz)IEC 60068-2-6	
Shock Resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27	

Ordering and shipping details

Category	22468-PUSHBUTTONS,22MM(METAL) NEW	
Discount Schedule	CS2	
Gtin	00785901371229	
Returnability	No	
Country Of Origin	FR	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov