

ZB5AW811723

white flush/black flush illuminated double-headed
pushbutton Ø22 unmarked

Price** : 29.00 USD



ZB5AW811723 has not been replaced. Please contact your customer care center for more information.

⚠ Discontinued

Main

Range of product	Harmony XB5
Product or component type	Head for illuminated double-headed push-button
Product compatibility	Integral LED
Device short name	ZB5
Bezel material	Plastic
Mounting diameter	0.87 in (22 mm)
Sale per indivisible quantity	1
Shape of signaling unit head	Rectangular
Type of operator	spring return
Operator profile	2 flush push-buttons - 1 central pilot light
Operators description	White unmarked - black unmarked

Complementary

CAD overall width	1.10 in (28 mm)
CAD overall height	1.85 in (47 mm)
CAD overall depth	1.26 in (32 mm)
Net weight	0.05 lb(US) (0.022 kg)
Operator profile	Black flush, unmarked White flush, unmarked
Mechanical durability	1000000 cycles

Environment

Protective treatment	TH
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class II IEC 60536
IP degree of protection	IP40
NEMA degree of protection	NEMA 13 NEMA 4X
Resistance to high pressure washer	1015.26 psi (7000000 Pa) 131 °F (55 °C) 0.1 m
IK degree of protection	IK05 IEC 50102

Standards	EN/IEC 60947-1 EN/IEC 60947-5-4 EN/IEC 60947-5-1 JIS C8201-5-1 CSA C22.2 No 14 UL 508 JIS C8201-1
Product certifications	UL listed GL RINA CSA BV DNV LROS (Lloyds register of shipping)
Vibration resistance	5 gn 2...500 Hz)IEC 60068-2-6
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27

Ordering and shipping details

Category	22467-PUSHBUTTONS,22MM(PLASTIC) NEW
Discount Schedule	CS2
GTIN	00785901388272
Package weight(Lbs)	0.04 lb(US) (0.019 kg)
Returnability	No
Country of origin	FR

Contractual warranty

Warranty	18 months
----------	-----------