Product data sheet

Specification





Light block, Harmony XB4, Harmony XB5, for head 22mm, universal LED, plug-in connector, 24V AC DC

ZBVB14

Product availability: Stock - Normally stocked in distribution facility

Price*: 57.00 USD

Main

Range Of Product	Harmony XB4 Harmony XB5
Product Or Component Type	Light block
Device Short Name	ZBV
Sale Per Indivisible Quantity	5
Connections - Terminals	Plug-in connector
Signalling Type	Steady
Light Source	Universal LED
Bulb Base	Integral LED
Light Block Supply	Direct
Light Source Colour	White
[Us] Rated Supply Voltage	24 V AC/DC 50/60 Hz

Complementary

Complementary	
Net Weight	0.04 lb(US) (0.016 kg)
Supply Voltage Limits	19.230 V DC 21.626.4 V AC
Current Consumption	18 mA
Service Life	100000 h at rated voltage and 25 °C
Surge Withstand	1 kV IEC 61000-4-5
Mounting Of Block	Front mounting
Electrical Composition Code	M1 M2 M3 M4 M5 M6 M10 MF1 P1 P2 PF1

Environment

Protective Treatment TH

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C)
Ip Degree Of Protection	IP20 IEC 60529
Standards	EN/IEC 60947-1 CSA C22.2 No 14 EN/IEC 60947-5-5 UL 508 JIS C8201-5-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 JIS C8201-1
Resistance To Fast Transients	2 kV IEC 61000-4-4
Resistance To Electromagnetic Fields	9.14 V/m (10 V/m) IEC 61000-4-3
Resistance To Electrostatic Discharge	6 kV on contact (on metal parts) IEC 61000-4-2 8 kV in free air (in insulating parts) IEC 61000-4-2
Electromagnetic Emission	Class B IEC 55011
[Us] Rated Supply Voltage	24 V

Ordering and shipping details

Category	US10CS222469
Discount Schedule	0CS2
Gtin	3389110090147
Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.13 in (5.400 cm)
Package 1 Width	1.69 in (4.300 cm)
Package 1 Length	2.05 in (5.200 cm)
Package 1 Weight	0.25 oz (7.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	2.13 in (5.400 cm)
Package 2 Width	1.69 in (4.300 cm)
Package 2 Length	2.05 in (5.200 cm)
Package 2 Weight	1.45 oz (41.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	200
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.24 lb(US) (1.923 kg)

Contractual warranty

Warranty

18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·


Product data sheet

ZBVB14

Dimensions Drawings

Dimensions

with ZB5AZ009 Fixing Collar



with ZB4BZ009 Fixing Collar

