

ZCE06

limit switch head ZCE - cat's whisker with nitrile boot

Product availability : Stock - Normally stocked in distribution facility



Price** : 17.00 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Multi-directional head
Product compatibility	XCKD XCKP XCKT XCMD
Associated body	ZCMD25L5 ZCD26 ZCD39 ZCMD21C12 ZCMD39L5 ZCP31 ZCMD37L5 ZCMD29L5 ZCMD21L2 ZCT21G11 ZCT27P16 ZCMD29C12 ZCT25G11 ZCT21P16 ZCMD25L1 ZCD29 ZCD21M12 ZCMD29L2 ZCT26P16 ZCMD21L1 ZCMD29L1 ZCP21M12 ZCT28N12 ZCMD61C12 ZCMD37L2 ZCMD25L2

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

ZCP35
 ZCMD41L5
 ZCT26N12
 ZCMD81L2
 ZCD35
 ZCD29M12
 ZCP39
 ZCMD39L2
 ZCT27G11
 ZCMD69C12
 ZCT25N12
 ZCMD41L1
 ZCP26
 ZCD25
 ZCD31
 ZCMD39L1
 ZCMD37L1
 ZCMD81L5
 ZCT26G11
 ZCD37
 ZCMD41L2
 ZCT27N12
 ZCMD21M12
 ZCT28G11
 ZCD28
 ZCMD61M12
 ZCP29
 ZCMD21L08U78
 ZCMD21L08R12
 ZCP25
 ZCT25P16
 ZCP29M12
 ZCD27
 ZCP28
 ZCP27
 ZCT21N12
 ZCMD81L1
 ZCP37
 ZCP21
 ZCMD21L5
 ZCD21
 ZCT28P16

Movement of operating head	Multi-directional
Type of operator	Cat"'s whisker spring return metal with nitrile boot)
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without

Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901497479
Package weight(Lbs)	0.04 kg (0.08 lb(US))
Returnability	Yes
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------