

# ZCE10

## limit switch head ZCE - metal end plunger

Product availability : Stock - Normally stocked in distribution facility



Price\*\* : 7.80 USD



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKT XCKD XCKP
Associated body	ZCD37 ZCMD37L1 ZCP27 ZCT27G11 ZCMD21C12 ZCD35 ZCMD37L2 ZCMD21L2 ZCD31 ZCMD25L5 ZCT26N12 ZCMD81L2 ZCT28G11 ZCD28 ZCD27 ZCT21N12 ZCMD41L2 ZCD26 ZCMD37L5 ZCMD21M12 ZCT26P16 ZCP29M12 ZCMD41L1 ZCD29M12 ZCD21 ZCMD29L1 ZCMD29L5 ZCT21G11

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCP21M12  
 ZCMD61C12  
 ZCMD81L5  
 ZCMD39L5  
 ZCT27N12  
 ZCT25G11  
 ZCMD29C12  
 ZCMD21L08U78  
 ZCMD25L2  
 ZCD39  
 ZCP26  
 ZCP29  
 ZCMD69C12  
 ZCP39  
 ZCP25  
 ZCT25N12  
 ZCMD25L1  
 ZCT28N12  
 ZCT27P16  
 ZCP35  
 ZCD25  
 ZCMD39L1  
 ZCD29  
 ZCT26G11  
 ZCD21M12  
 ZCMD21L1  
 ZCT21P16  
 ZCMD41L5  
 ZCP37  
 ZCP28  
 ZCMD21L08R12  
 ZCP21  
 ZCMD29L2  
 ZCT25P16  
 ZCMD81L1  
 ZCMD39L2  
 ZCMD61M12  
 ZCP31  
 ZCMD21L5  
 ZCT28P16

Movement of operating head	Linear
Type of operator	End plunger spring return metal
Type of approach	Vertical approach, 1 direction

### Complementary

Positive opening	With
------------------	------

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901449980
Package weight(Lbs)	0.01 kg (0.02 lb(US))
Returnability	Yes
Country of origin	ID

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

**Contractual warranty**

Warranty	18 months
----------	-----------