

# ZCE28

limit switch head ZCE - roller lever plunger  
horizontal or vertical direction

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 21.00 USD



## Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCMD XCKT XCKP XCKD
Associated body	ZCMD21C12 ZCMD21L08U78 ZCMD25L5 ZCT21G11 ZCMD41L1 ZCT27P16 ZCD29M12 ZCD21 ZCP37 ZCMD41L2 ZCD25 ZCMD21L5 ZCMD39L1 ZCP27 ZCP35 ZCP28 ZCT28G11 ZCT26N12 ZCD39 ZCT25G11 ZCMD39L5 ZCT21P16 ZCP25 ZCMD81L1 ZCD31 ZCT28P16

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

ZCMD81L5  
 ZCMD69C12  
 ZCT27N12  
 ZCD21M12  
 ZCT25N12  
 ZCD26  
 ZCP21M12  
 ZCP39  
 ZCMD25L1  
 ZCT25P16  
 ZCT21N12  
 ZCP29  
 ZCMD37L2  
 ZCMD61C12  
 ZCD28  
 ZCD37  
 ZCT26G11  
 ZCP21  
 ZCMD81L2  
 ZCMD37L1  
 ZCMD25L2  
 ZCP29M12  
 ZCMD29L1  
 ZCMD37L5  
 ZCMD41L5  
 ZCMD21M12  
 ZCT28N12  
 ZCT26P16  
 ZCMD21L08R12  
 ZCMD21L1  
 ZCP26  
 ZCD27  
 ZCMD29L2  
 ZCT27G11  
 ZCMD39L2  
 ZCMD61M12  
 ZCP31  
 ZCD35  
 ZCMD21L2  
 ZCMD29C12  
 ZCMD29L5  
 ZCD29

Movement of operating head	Linear
Type of operator	Roller lever plunger spring return thermoplastic
Type of approach	Lateral or vertical approach, 1 direction

### Complementary

Switch actuation	By 30° cam
Positive opening	With

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22413 - LIMIT SWITCH, IEC, MINIATURE
Discount Schedule	T
GTIN	00785901497639
Package weight(Lbs)	0.36 kg (0.8 lb(US))
Returnability	No
Country of origin	ID

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisononyl phthalate (DINP) which is known to the State of California to cause Carcinogen + Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------