

ZCKE095

limit switch head ZCKE - w/o lever stay put left
and right actuation - +120 °C

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 59.00 USD



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Rotary head
Product compatibility	XCKJ
Associated body	ZCKJ9H29 ZCKJD31H7 ZCKJ2 ZCKJ9H7 ZCKJD31H29 ZCKJD39H7 ZCKJ1H7 ZCKJ11 ZCKJ9 ZCKJD39 ZCKJ21 ZCKJ2H29 ZCKJ11H29 ZCKJ1H29 ZCKJ2H7 ZCKJ11H7 ZCKJ21H7 ZCKJD39H29 ZCKJ1 ZCKJD31 ZCKJ21H29
Movement of operating head	Rotary
Type of operator	Stay put without operating lever stay put
Type of approach	Lateral approach, 2 directions

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Complementary

Switch actuation	From left and right
Positive opening	With
Net weight	0.42 lb(US) (0.19 kg)
Head material	Metal

Environment

Ambient air temperature for operation	50...248 °F (10...120 °C)
Ambient air temperature for storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	00785901195207
Package weight(Lbs)	0.36 kg (0.8 lb(US))
Returnability	No
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.p65warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations

Contractual warranty

Warranty	18 months
----------	-----------