

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 109.00 USD



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch body
Device short name	ZCKJ
Body type	Fixed
Product compatibility	XCKJ
Associated head	ZCKE05 ZCKE06 ZCKE08 ZCKE21 ZCKE23 ZCKE61 ZCKE619 ZCKE62 ZCKE629 ZCKE63 ZCKE64 ZCKE65 ZCKE66 ZCKE67
Body material	Metal
Cable entry	1 entry tapped for 1/2" NPT cable gland
Number of poles	2
Contacts type and composition	2 C/O
Contact operation	Snap action
Number of steps	1 1 position
Contacts material	Gold plated contacts

### Complementary

Local display	Without
---------------	---------

Electrical connection	Screw-clamp terminals, clamping capacity: 1 x 0.75...2 x 1.5 mm <sup>2</sup>
Positive opening	Without
Minimum actuation speed	0.01 m/min
[Ie] rated operational current	3 A at 240 V, AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V, DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 V conforming to CSA C22.2 No 14 contact block 300 V conforming to UL 508 contact block 500 V degree of pollution 3 conforming to IEC 60947-1 contact block
Resistance across terminals	0.25 mOhm conforming to IEC 60255-7 category 3
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60664 6 kV conforming to IEC 60947-1
Short-circuit protection	10 A by gG cartridge fuse
Width	1.57 in (40 mm)
Height	4.02 in (102 mm)
Depth	2.36 in (60 mm)
Product weight	1 lb(US) (0.455 kg)
Terminals description ISO n°1	(11-12)NC (13-14)NO (21-22)NC (23-24)NO

## Environment

IP degree of protection	IP66
IK degree of protection	IK07
Ambient air temperature for operation	50...248 °F (10...120 °C) high temperature
Ambient air temperature for storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

## Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003389119044486
Nbr. of units in pkg.	1
Package weight(Lbs)	0
Returnability	N
Country of origin	FR

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1010 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------