

# Product data sheet

## Characteristics

# ZCKY19

limit switch lever ZCKY - metal roller lever - -25..  
+70°C

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 2.70 USD



### Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch lever
Device short name	ZCKY
Product compatibility	XCKP XCKT
Associated head	ZCKD05
Movement of operating head	Rotary
Type of operator	Roller lever spring return metal (-)
Type of approach	Lateral approach

### Complementary

Switch actuation	By 30° cam
Positive opening	With

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C) standard environment
Ambient air temperature for storage	-40...158 °F (-40...70 °C) standard environment
Environmental characteristic	Standard environment

### Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003389110599787
Nbr. of units in pkg.	1

Package weight(Lbs)	5.999999999999998E-2
Returnability	N
Country of origin	FR

**Offer Sustainability**

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

**Contractual warranty**

Warranty period	18 months
-----------------	-----------