Product data sheet

Specifications



Current limiter,TeSys Deca Frame 2,32A/690V,activation 1.5kA,at top of GV2ME/GV2P/GV2RT with screw clamp connections

GV1L3

Product availability: Stock - Normally stocked in distribution facility

Price*: 117.00 USD

Main

Range	TeSys
Range Of Product	TeSys GV2 TeSys Deca
Accessory / Separate Part Category	Protection accessory
Product Or Component Type	Current limiting module
Range Compatibility	TeSys GV2 TeSys Deca
Product Compatibility	GV2RT GV2ME GV2P GV2L
Function Of Module	Increasing the breaking capacity of a circuit breaker
Mounting Location	On top of the circuit breaker
[Ie] Rated Operational Current	32 A
[Ith] Conventional Free Air Thermal Current	63 A IEC 60947-1
Activation Threshold	1500 A
Breaking Capacity	<= 100 kA depending on protective device
[Ue] Rated Operational Voltage	690 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	690 V AC 50/60 Hz IEC 60947-1

Complementary

Connections - Terminals	Screw clamp terminals 1 x 0.00…0.04 in² (1.5…25 mm²) rigid Screw clamp terminals 2 x 0.00…0.02 in² (1.5…10 mm²) rigid Screw clamp terminals 1 x 0.00…0.04 in² (1.5…25 mm²) flexible without cable end Screw clamp terminals 2 x 0.00…0.02 in² (1.5…10 mm²) flexible without cable end Screw clamp terminals 1 x 0.00…0.02 in² (1.5…16 mm²) flexible with cable end Screw clamp terminals 2 x 0.00…0.01 in² (1.5…4 mm²) flexible with cable end
Tightening Torque	19.47 lbf.in (2.2 N.m)
Net Weight	0.29 lb(US) (0.13 kg)

Ordering and shipping details

Category	US10I1122366
Discount Schedule	0I11
Gtin	3389110209952

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	Yes
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.35 in (8.5 cm)
Package 1 Width	1.97 in (5.0 cm)
Package 1 Length	3.15 in (8.0 cm)
Package 1 Weight	4.30 oz (122.0 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	24
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	5.91 in (15.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	6.84 lb(US) (3.104 kg)

Contractual warranty

Warranty	18 months

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >

Transparency

RoHS/REACh

Well-being performance

Reach Free Of Svhc	
Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Connections and Schema

Current Limiter
GV1L3