





Transformer, dry type, encapsulated, 1.5kVA, 1 phase, 277V primary, 120/240V secondary, 8A, 115C rise

1.5S8F

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 2,104.00 USD

Main

Product Or Component Type	Dry Sealed Transformer
Primary To Secondary Voltage	277 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	8A
Phase	1 phase
Power Rating	1.5 kVA
Temperature Rise	115 °C
Height	8.25 in (209.55 mm)
Width	8.68 in (220.47 mm)
Depth	6.56 in (166.62 mm)
Enclosure Mounting	Wall mounted
Enclosure Material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation Temperature	356 °F (180 °C)
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	US10PE216277
Discount Schedule	0PE2
Gtin	785901338321
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCI
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Number Of Units In Package 1	1
Package 1 Height	9.70 in (24.638 cm)
Package 1 Width	11.00 in (27.94 cm)
Package 1 Length	12.80 in (32.512 cm)
Package 1 Weight	30.00 lb(US) (13.608 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
⊘	Mercury Free
②	Rohs Exemption Information Yes
⊘	Pvc Free

Certifications & Standards

REACh Declaration
Compliant
EU RoHS Declaration
China RoHS declaration
Pro-active China RoHS declaration (out of China RoHS legal scope)
Product Environmental Profile
No need of specific recycling operations
WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov