# Product data sheet

Specifications

## PUSH BUTTON 600VAC 10A 30MM T-K

9001K2L3G20H13

Discontinued on: Oct 11, 2019

Discontinued

## Main

| | |
|---|---|
| **Bezel Material** | Chromium plated metal |
| **Device Short Name** | K |
| **Mounting Diameter** | 1.18 in (30 mm) |

## Complementary

| | |
|---|---|
| **Line Rated Current** | 10 A |
| **Operator Position Information** | 2 positions |
| **Operator Profile** | 1 projecting push-button |
| **Utilisation Category** | AC-15<br>DC-13 |

## Environment

| | |
|---|---|
| **Nema Degree Of Protection** | NEMA 1/2/3/3R/4/6/12/13 |
| **Product Certifications** | UL listed file E42259 CCN NKCR<br>CE<br>CSA LR24590 class 3211 03 |

## Ordering and shipping details

| | |
|---|---|
| **Category** | 21426-9001 K (NOT KA,KM,KX) |
| **Discount Schedule** | CS1 |
| **Returnability** | No |
| **Country Of Origin** | MX |

## Contractual warranty

| | |
|---|---|
| **Warranty** | 18 months |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.