

Product data sheet

Specifications

Multi9 - comb busbar - 3L - 18 mm pitch - 12 modules - 100A



10173

⚠ Discontinued on: May 7, 2019

⚠ End-of-service on: Sep 21, 2020

⚠ Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	Multi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	12

Complementary

Number Of Ways	4 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	2.13 in (54 mm)
Insulation	Insulated
Device Presentation	Uncuttable
[Ie] Rated Operational Current	100 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	240 V AC 50/60 Hz
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz UL 508
[Uimp] Rated Impulse Withstand Voltage	12 kVUL 508
Mounting Location	Top tunnel type terminals
9 Mm Pitches	24
Width	8.50 in (216 mm)
Color	White RAL 9001)
Range Compatibility	Multi9 Multi9 C60 C60 UL489

Environment

Standards	UL 508
Fire Resistance	1760 °F (960 °C) 30 s) UL 508

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	US10DE200908
Discount Schedule	0DE2
Gtin	00785901895527
Returnability	No
Country Of Origin	DE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.61 in (4.1 cm)
Package 1 Width	3.74 in (9.5 cm)
Package 1 Length	9.33 in (23.7 cm)
Package 1 Weight	30.16 oz (855 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
<hr/>		
Eu Rohs Directive		Compliant EU RoHS Declaration
<hr/>		
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
<hr/>		
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
<hr/>		