

# Product data sheet

Specifications

## Multi9 - comb busbar - 3L - 18 mm pitch - 12 modules - 80A



10183

⚠ Discontinued on: Sep 8, 2020

⚠ End-of-service on: Sep 22, 2020

⚠ Discontinued

### Main

Range	Multi9
Product Or Component Type	Comb busbar
Mounting Mode	Horizontal
Accessory / Separate Part Category	Connection accessory
Lines Description	3L
Length In 18 Mm Modules	12

### Complementary

Number Of Ways	4 ways 3 L
Poles Configuration For 1 Way	1 x 3P
Connection Pitch	0.71 in (18 mm)
Connector Type	tooth
Distance Between Way	2.13 in (54 mm)
Insulation	Insulated
Device Presentation	Uncuttable
[Ie] Rated Operational Current	80 A 104 °F (40 °C)
[Ue] Rated Operational Voltage	480 V AC 50/60 Hz Ph/Ph 277 V AC 50/60 Hz Ph/N
[Ui] Rated Insulation Voltage	1000 V AC 50/60 Hz UL 508
[Uimp] Rated Impulse Withstand Voltage	12 kVUL 508
Mounting Location	Top tunnel type terminals
9 Mm Pitches	24
Width	8.50 in (216 mm)
Color	White RAL 9001)
Range Compatibility	Multi9 Multi9 C60 C60 UL489

### Environment

Standards	UL 508
Fire Resistance	1760 °F (960 °C) 30 s ) UL 508

### Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Category	00908-C60N SUPPLEMENTARY PROTECTORS
Discount Schedule	DE2
Gtin	3606480385940
Returnability	No
Country Of Origin	DE

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.05 in (5.2 cm)
Package 1 Width	4.41 in (11.2 cm)
Package 1 Length	9.17 in (23.3 cm)
Package 1 Weight	32.03 oz (908 g)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.	